RF Adapter

pro-SIGNAL

Specifications

Convert From Coax Type	: BNC
Convert From Gender	: Plug
Convert To Coax Type	: F
Convert To Gender	: Jack
Adapter Body Style	: Straight Adapter
Impedance	: 50Ω
Connector Type	: Inter Series Coaxial

Diagram

3/8-32UNEF-2A
Ø14.5
Ø10
15
10.7
32.6

No.	Part Name	Material	Finish	Qty.
1	Shell	Note 1	Note 2	
2	Housing			
3	Insulator	POM	White	
4	Contact Pin	Note 3	-	
5	Insulator	POM	White	1
6	Gasket	Rubber	Red	
7	Retainer Ring	Note 3	Note 2	
8	Spring	SK5		
9	Washer	Note 3		

Notes: Finish (Plating Thickness in Micro-Inches)

1. Zinc Diecast
2. Nickel PL. 100 min. Thick Over Copper PL. 50 min. Thick
3. Brass

Part Number Table

Description	Part Number
BNC-Male to F-Female Adapter - 10 Pack	27-9750

Dimensions : Millimetres

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-SIGNAL