LogiLink®

This USB-C cable built-in E-mark chip supports the devices intelligently to deliver the fastest charging up to 20 V/5 A (100 W) and provides the data transfer up to 480 Mbps.

» Supports Power Delivery 3.0 up to 100 W (20 V/5 A); with an E-mark chipest allows you to reliably power USB-C devices at the possible fastest speed
» Compatible with USB 2.0 standard for data transferring speed up to 480 Mbps
» Supports reversible USB-C connector
» Slim and elegant design with aluminum alloy body and unibody structure
» USB-C plug with gold plated connector and contacts provides a solid quality for connection
» Compatible with most USB-C enabled Laptop, smartphone and tablet devices

USB-C

Fast Charging

Tablet/Smartphone   Laptop

USB-C

100 W USB-C Power Adapter

PD3.0

100W
Power
Delivery

Double
Shielded

Gold
Plated

with E-mark

1.5 m
Cable Length

*The maximum power output is depending on the device to be charge and the power adapter used.

CUA0106

4 052792 062267
Made in China

LogiLink®

Art. No.: CUA0106

Specifications:

Connection 1	USB-C 3.2 (USB 2.0), male
Connection 2	USB-C 3.2 (USB 2.0), male
Connector Material	Gold-Plated
Data Transfer Rate	Up to 480 Mbps
Max. Current	Up to 5 A
Cable Length	1.5 m
Color	Black/Grey

TPE JACKET
32AWGX1P
32AWGX2C
22AWGX2C
AM&BRAID(22AWG)

Package Content:
» 1x USB-C 3.2 (USB 2.0) Cable

Package Information:
» Packing Dimension: 193x177x14 mm
» Packing Weight: 0.05 kg
» Carton Dimension: 420x380x220 mm
» Carton Q'ty: 100 pcs
» Carton Weight: 6.4 kg

PIN ASSIGNMENT:

USB C TYPE(P1)	E-MARK	USB C TYPE(P2)	
A5		A5	cc
B5		B5	cc
A6		A6	Dp1
A7		A7	Dn1
A4,B4,A9,B9		A4,B4,A9,B9	Vbus
A1,B1,A12,B12		A1,B1,A12,B12	GND
SHELL		SHELL	

RoHS compliant CE

CUA0106

4 052792 062267

Made in China