



DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STS	REV	SVP	DHB						
30JA02	R	02	-	-	-	BASE SHROUD MAT'L CHANGED FROM PM002205 PBT GF15 TO M4698 PBT GF30 & ADDED NOTES 13 PLUS1	229849	RVP	RVP	JH
30JA03	R	02	AA	-	-	ADDED MOUNTING DETAIL INFORMATION	230501	RVP	RVP	JH
04FE03	R	02	AB	-	-	ADDED NOTES 7 & 8, ADDED BLACK SQUARES TO RLSS1, REMOVED OPTIONAL CONSTRUCTION AND REMOVED INSPECTION SYMBOLS	230434	JBR	EOV	JH
19MR08	R	02	AC	-	*	OBSOLETED- REPLACED BY 12577941	404156	TMP	TMP	RTM
03APO8	R	02	AD	-	-	REINSTATED	404257	EAJ	TRB	RTM

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
   DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. SEALING CODE O - GASKET IS USED TO MINIMIZE DUST AND PRACTICE INTRUSION.
3. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
4. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
   CONNECTOR 12065844
5. SHROUD CAN BE MOUNTED USING THREADED FASTENERS THAT CAN BE APPLIED TO A 6MM HOLE AND MUST BE APPLIED USING A TORQUE BETWEEN 5 NM AND 6.5NM.
6. DIMENSIONS NOT INDICATED BY " ■ " DO NOT REQUIRE INSPECTION AND ARE FOR REFERENCE ON THIS DRAWING. THESE DIMENSIONS MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.
7. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.

DRAWING NUMBER 12176538

SIZE	SCALE	FRAME	SHEET	SHEETS	REV	SVP
A1x3	2:1	2 OF 2	1 OF 1	R	02	AD

DWG TYPE: PART DRAWING

STYLE

VOLUME (CM³) | SYSTEM USED: D

UNLESS OTHERWISE SPECIFIED
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED.
THIS DOCUMENT CONTAINS DELPHI PROPRIETARY INFORMATION AND RELATED SYSTEMS WHICH WILL, TALE PRECEDENCE FROM ITS ISSUANCE. THIS DOCUMENT IS TO BE RETURNED UPON REQUEST. IT SHALL NOT BE REPRODUCED OR DISTRIBUTED OR DEVIATION TOLERANCES ARE NOT ALLOWED UNLESS SPECIFICALLY APPROVED IN WRITING BY DELPHI PROPRIETARY. NO RIGHTS ARE GRANTED BY KNOWLEDGE OF DELPHI PROPRIETARY.
ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE

N/A PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

| ATMOSPHERICAL PRESSURE (MB) | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aptiv:
12176538