XY308-2.54



Dimensions		
Poles:	2P,3P-12P	
Pitch:	2.54mm(.100")	
Electrical		
Standard:	UL	IEC
Voltage Rating:	150V	130V
Current Rating:	6A	8A
Wire range:	26-18AWG	1.0mm²
Withstand voltage	AC1250V/Min	
Mechanical		
Torque:	0.1N.m(0.9Lb-In.)	
Ambient temperature	-40°C~+105°C	
Strip length	4.5mm	
Material		
Housing:	PA66(UL 94V-0)	
Pin header:	Brass,Tin Plated	
Wire Cage:	Brass,Nickel Plated	
Screw:	M1.6,steel,A3 Zn plated	