

Features

- Instrument Glass Window
- Inbuilt restrictor screw.
- Copper Alloy Element & Movement
- Stainless Steel case with G 3/8 in. BSPM (32mm flats)
- Bottom entry connection
- Ambient Operating Temperature between -20 and +60°C
- Operating Temperature (Medium) +60°C
- 1.6 Per DIN 16005 Accuracy Class
- Calibrated versions available

RS PRO Analogue

RS Stock No.: 188-986



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

100mm Diameter Dual-Scale Pressure and Vacuum Gauge

A general purpose gauge suitable for all gaseous and liquid media that will not destruct the pressure system or attack copper alloy parts.

•

General Specifications

Maximum Pressure Measurement	0bar
Minimum Pressure Measurement	-1bar
Mounting Type	Bottom Entry
Display Type	Analogue
Connection Size	BSP 3/8
Gauge Outside Diameter	100mm
Case Material	Stainless Steel
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+60°C
Pressure Gauge Type	Dial

