



SPECIFICATIONS:

- MOVABLE CONTACT: Copper alloy, silver plated
- TERMINALS: Copper alloy, silver plated
- RATING: 5Amps with resistive load @ 125VAC or 28VDC
2Amps with resistive load @ 250VAC
- CONTACT RESISTANCE: 10m-ohms max. initial
- INSULATION RESISTANCE: 1,000M-ohms min.
- DIELECTRIC STRENGTH: 1,500V RMS @ sea level
- ELECTRICAL LIFE: 50,000 make and break cycles at full load
- OPERATING TEMPERATURE: -30°C to $+85^{\circ}\text{C}$

Rev.	Date	Description	Remark
YUBRIGHT		YUBRIGHT CO., LTD.	
Title		TOGGLE SWITCH	
Date		20130208	
Rev.		A	
File		SWT030	
Dwg. No.		SARU0030120701	
P/N		SA-RU0030.1207	
RoHS		✓	
App.		b37	
File		SWT030	
Rev.		A	
App.		b37	
File		SWT030	

Unless otherwise specified, demensions are in millimeters.