

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0433751001**
Status: **Active**
Overview: Sabre Power Connector
Description: Sabre Double Crimp Terminal, Female, Double 18 AWG, 4.57mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact with TPA

Documents:

Drawing (PDF)	Test Summary 444410000-TS-000 (PDF)
Product Specification PS-44441-9999-001 (PDF)	Datasheet (PDF)
Packaging Specification 433750000-PK-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	43375
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	For double crimping of 18 AWG wire in a side-by-side orientation. Terminal mates to 3.18mm wide x 0.51mm thick flat blade PC tab. Allows 44441 receptacle housings to comply with the UL1977 finger proof access requirement
Crimp Quality Equipment Overview	Yes
Product Name	Sabre Power Connector
UPC	Sabre 800754365994

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.360/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.57mm max.
Wire Size AWG	14, 16, 18+18
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	433750000-PK-000
Product Specification	PS-44441-9999-001
Sales Drawing	SD-43375-1001-001
Test Summary	444410000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

43375 Series

Use With

44441 Receptacle Housings

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Sabre Female Terminals 14-18 AWG or Double 18 AWG (vertical)	638117300
Extraction and Activation Tool	638132700
Terminator Die - Doubles	638405200
Mini-Mac Applicator	638916100

Mini-Mac Applicator, [638917000](#)
For Narrow
Insulation Crimp

This document was generated on 08/12/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION