



ENGLISH

Datasheet

Stock No: 569-767

RS Pro P13.5s Filament Indicator Lamp, Clear, 2.4 V, 0.5 A, 15h



Product Details

P13.5s Olive Prefocus Vacuum

General purpose torch lamp

Olive shape B3 1/2 - 11mm glass

P13.5s prefocus base

Vacuum



ENGLISH

Torch Lamps

Filament lamps will perform to specification and give optimum life when: they are powered at the rated voltage from a stabilised 50Hz ac supply; the ambient temperature is in the range +20°C to +25°C; and no mechanical vibration is present.

Deviations from these criteria can have a significant effect on lamp life, particularly with low current filaments (<80 mA).

Operation from a dc. supply at rated voltage can reduce specified life by up to 50%.

The effect of variation from the rated operating voltage should be noted: 5% above will reduce lamp life by up to 50%; and 5% below will significantly increase lamp life.

Current consumption can vary by up to $\pm 10\%$ on stated values at rated supply voltage. Care therefore should be exercised when running a number of lamps in series. In such applications it is recommended that the rated voltage be reduced by 10% to prevent premature failure of individual lamps.

Conversion of light output units: Lumens = MSCP x 12.6, MSCP = Lumens / 12.6.

Specifications:

Voltage Rating	2.4 V
Lamp Base	P13.5s
Current Rating	0.5 A
Diameter	11mm
Length	28 mm
Lens Colour	Clear
Luminosity	11 lm
Life Hours	15h