

Product specifications **A252931**

Last update: 3/11/2015 4:44:06 PM

**General**

Description	Dunlop Acifort Ribbed full safety
Upper/Sole Color	Black/Red
Status	Stock,
Segment	Construction&Infra
Product line	
Sizerange/#	40-47/8
Hangtag	
Insole	
Lining	Grey polyamide (nylon) - Sanitized
Resistance code	3

**Safety**

Standard	EN ISO 20345:2011.SB.P.A.FO.SRA
	<input checked="" type="checkbox"/> Steel Toecap <input checked="" type="checkbox"/> Antistatic
	<input checked="" type="checkbox"/> Steel Midsole <input type="checkbox"/> Energy absorbing
	<input checked="" type="checkbox"/> Oilresistant sole <input type="checkbox"/> Cold insulating
Safety marking Manual	Dunlop EN manual

Sole info

Sizing	<input checked="" type="checkbox"/> French <input checked="" type="checkbox"/> English <input checked="" type="checkbox"/> U.S.
Date of manufacturing	<input checked="" type="checkbox"/>
Other sole info	CE Dunlop Made in P. Pict.

Labeling/marking

Marking	Dunlop stamp
Barcode on boot	Barcode label
Barcode packaging	Dunlop label
Barcode outercarton	Dunlop label

Remark

Weight 43: 2,64 kg/pr

Packaging		Polybag						
Size	Boxtype	Length	Width	Height	Pairs/Box	Boxes/layer	#Layers	Pallet height
40-42	PT19	585	397	295	6	4	6	1.95
43-44	PT20	585	397	315	6	4	5	1.75
45-47	PT6	585	435	345	6	4	4.5	1.91