

Specifications of UT330T USB Temperature datalogger

Specifications	UT330T
Measurement range	-30~70°C
measurement accuracy	±0.4°C
IP rating	IP65
Resolution	0.1°C
Data storage	64000 groups
Cyclic recording	support
Sampling interval	10s~24h adjustable
Unit/alarm Settings	Unit default °C; Alarm type is divided into single/accumulated alarm, single alarm by default
starting mode	Button/software (immediate, delay, timing)
Recording delay	0min~240min (the default 0), PC software can be set
Alarm delay	0s~10h (the default 0), PC software can be set
Auto power off	10s
General Characteristics	
Power	CR2032
Display	23mm x 20mm
Product net weight	41g
Product size	98mm x 38m x 14mm
Standard accessories	Batteries, bracket, screws, stickers, English manual
Standard individual packing	Gift box