

**A-series
ZQV 4N/10 BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	ZQV 4N/10 BL
Order No.	1528230000
GTIN (EAN)	4050118333138
Qty.	20 pc(s).

Data sheet

A-series ZQV 4N/10 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	58.7 mm	Width (inches)	2.311 inch
Height	2.8 mm	Height (inches)	0.11 inch
Depth	27.95 mm	Depth (inches)	1.1 inch
Net weight	7.556 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	Wemid	Colour	blue
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	2434520000_BED-ANL.ZQV_A_REIHE.pdf StorageConditionsTerminalBlocks