

NEW

Parallel female thread coupler



Technical characteristics

Technology: "One push" safety system (avoids hose whip)

Operating pressure: 2 to 12 bar


Flow rate at 6 bar: 3686 l/min ($\Delta P = 0,6$ bar)

ID Passage: 11 mm

Temperature: -15°C to +70°C

Construction: Polyamide composite body

Highlight: Anti-static, Excellent efficiency, Non scratch

	BSPP female thread	Parts Numbers
	G 3/8	ISI 111102EB
	G 1/2	ISI 111103EB
	G 3/4	ISI 111104EB