

**ARCA 405021W**



Sample photo

**Order symbol:** ARCA 405021W  
**Product nbr:** 8120145  
**Description:** Cabinet, PC  
**Remarks:** Cover with window, 2-point locking

**EAN:** 6418074080165  
**EI. number:**  
 Finland: 3423224  
 Electric No. 8212092015  
 Denmark:  
 Electric No. Sweden: 2500143

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	400	500	210	MPP ARCA 4050	Mounting plate perforated (450x350x2 mm - 26x11 mm)
<b>inch:</b>	15.7	19.7	8.3	MPMP ARCA 5040	Mounting plate multiperforated (450x350x2 mm - □3.6 mm)
Materials:				MPX ARCA 5040	Mounting plate (450x350 mm)
<b>Material:</b>	Polycarbonate			DRS ARCA 405021	DIN rail frame set
<b>Base colour:</b>	RAL 7035 -light grey			IDS ARCA 4050	Inner door set
<b>Cover colour:</b>	RAL 7035 -light grey			PMK ARCA 50	Pole mounting kit
<b>Gasket material:</b>	Polyurethane			RCS ARCA 4050	Rain canopy set
Temperatures:				SBK ARCA 40	Support bar kit
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SBK ARCA 50	Support bar kit
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			DSP ARCA HLS	Door stopper ARCA, horizontal, left, small
<b>Temperature °F (short term):</b>	-40 ... 250 °F			DSP ARCA HRS	Door stopper ARCA, horizontal, right, small
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				
Accessories:				<b>Rating:</b>	
MPS ARCA 5040	Mounting plate (450x350x2 mm)			Ingress Protection (EN 60529): IP65	
				Impact Resistance (EN 62262): IK08	
				Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 94 5VA	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 4, 4X, 12 and 13	

