

Parallel female thread twin coupler



Technical characteristics

Technology: "One push" safety system (avoids hose whip)

Operating pressure: 2 to 12 bar


Flow rate at 6 bar: 1 820 l/min ($\Delta P = 0,6$ bar)

ID Passage: 7,4 mm

Temperature: -15°C to +70°C

Construction: Composite body

Highlight: Anti-static, Non scratch

	A (mm)	B (mm)	C (mm)	BSPP female thread	Parts Numbers
		150	97	23	G 3/8
	160	111	26	G 1/2	ESI 078103