



Malleable iron pipe fittings

1 ISO G4 Long sweep bend



Dimension	Code	a	b	z
• S 1/8	770 001 101	35	32	28
• V 1/8	770 001 201			
• S 1/4	770 001 102	40	36	30
• V 1/4	770 001 202			
• S 3/8	770 001 103	48	42	38
• V 3/8	770 001 203			
• S 1/2	770 001 104	55	48	42
• V 1/2	770 001 204			
• S 3/4	770 001 105	69	60	54
• V 3/4	770 001 205			
• S 1	770 001 106	85	75	68
• V 1	770 001 206			
• S 1 1/4	770 001 107	105	95	86
• V 1 1/4	770 001 207			
• S 1 1/2	770 001 108	116	105	97
• V 1 1/2	770 001 208			
• S 2	770 001 109	140	130	116
• V 2	770 001 209			
• S 2 1/2	770 001 110	176	165	149
• V 2 1/2	770 001 210			
• S 3	770 001 111	205	190	175
• V 3	770 001 211			
• S 4	770 001 112	260	245	224
• V 4	770 001 212			

1a ISO D4 Short bend



Dimension	Code	a	b	z
• S 1/4	770 011 102	30	30	20
• V 1/4	770 011 202			
• S 3/8	770 011 103	36	36	26
• V 3/8	770 011 203			
• S 1/2	770 011 104	45	45	32
• V 1/2	770 011 204			
• S 3/4	770 011 105	50	50	35
• V 3/4	770 011 205			
• S 1	770 011 106	63	63	46
• V 1	770 011 206			
• S 1 1/4	770 011 107	76	76	57
• V 1 1/4	770 011 207			
• S 1 1/2	770 011 108	85	85	66
• V 1 1/2	770 011 208			
• S 2	770 011 109	102	102	78
• V 2	770 011 209			
• S 2 1/2	770 011 110	115	115	88
• V 2 1/2	770 011 210			
• S 3	770 011 111	127	127	97
• V 3	770 011 211			
• S 4	770 011 112	165	165	129
• V 4	770 011 212			