



6159 Pointy Shear Cutters | Peak Shear

The **EDGE Pointy Shear Cutters 6159 offer outstanding accessibility for applications** ranging from microscopy to micro-electronics applications. This model's unique, pointy head allows users to get underneath delicate components and execute Flush EDGE cuts on hard-to-access wires.

- **Perfect for** fine mechanics, industrial electricians, mechatronics engineers and micro-electronics specialists.
- **The pointy head design** and its symmetrical tips have been specifically adapted to allow for maximum access and reach.
- **Flush EDGE:** Best for applications in which precision cuts are of paramount importance and perfect for use in close tolerance electronics.



Part No.		A mm / in	B mm / in	C mm / in	D mm / in	E mm / in	G mm / in	H mm / in	g
6159	Flush Edge	134 / 5.28	14 / 0.55	12.8 / 0.50	5.0 / 0.20	1.0 / 0.04	5.0 / 0.23	3.2 / 0.13	54.4



Flush EDGE cut: Expert shear cutting technology and a controlled edge misalignment of less than 0.2 mm to deliver a clean, smooth cut, on even the thinnest wires.

High-performance alloy steel body for excellent durability and long-lasting performance, with precision-ground cutting edges that are induction hardened at 63-65 HRC.

Return spring and opening limiter for smooth operation that help minimise hand fatigue.

Suitable for cutting:

- Copper wire
- Standard steel
- Plastics
- Glass fibre cables
- Cutting insulation
- Cables
- Ties
- Corded material of all types

Bi-material and ESD-safe dissipative handles that eliminate electrostatic build-up and permit a slow charge equalization.

