



### **Datasheet**

# RS PRO Free Receptacle Female 7 pin Solder OD 5.2-6.2mm

Stock No: 209-5718



RS Pro's range of Chrome plated Brass push-pull locking connectors offer exceptional quality that is found in many cutting-edge connectors, including full 360° EMC shielding and high mating life. As has become standard within the RS Pro brand you can expect high quality products but at a reasonable price. These connectors are ideal for use in medical devices, testing equipment, audio equipment and other high-end indoor applications.

## **Features & Benefits:**

- Push-pull latching system
- Chrome plated Brass
- IP50
- 360° Screening for full EMC shielding
- 7A Current Rating

#### **Technical**

Characteristics	Value Standard		
Endurance	>5000cycles	IEC60512-5test9a	
Humidity	Up to 95% at 60°C		
Temperature range	-55°C, +250°C		
Resistance to vibration	10-2000Hz,15g IEC 60512-4 test 6d		
Shock resistance	100g, 6ms	IEC 60512-4 test 6c	
Salt spray corrosion test	>96hrs	IEC 60512-6 test 11f	
Protection index (mated)	IP50	IEC 60529	
Climatical category	55/175/21	IEC 60068-1	


#### **Electrical**

Characteristics		Value	Standard
Shielding	at 10MHZ	>75 dB	IEC 60619-1-3
efficiency	at 1GHZ	>40 dB	IEC 60619-1-3





# **Dimensional line drawings**























2(\$1.3)

 $4(\phi 0.9)$ 

5 (\$0.9)

7(\$0.7)

8(\$0.7)

10 (Ø0.5)

14 (\$0.5)

16 (\$0.5)

# **Quality Standards**







