



WOYR2.E23301 Switches, Special Use - Component

Enhanced searching capability for this category can be found in UL's iQ Family of Databases (iq.ul.com).

[Page Bottom](#)

Switches, Special Use - Component

[See General Information for Switches, Special Use - Component](#)

ZF ELECTRONICS CORP

E23301

11200 88TH AVE

PLEASANT PRAIRIE, WI 53158 USA

Cat. No.	Amps	Volts	Hz	Load	Endurance	Temp C	POL/THR	Per Pole/Circuit Code	SPCOA
PR Series, f/b K, f/b 2, f/b 2 or 3, f/b J, f/b 5, f/b B, C, D, E, F, G, or W, f/b B, W, Y, G, U, or O, f/b B, R, Y, or W, f/b N, f/b N: *									
	6	125	60	GP	6K	65	1/1	-/-	-
A23* w w/o prefix letter									
	5	125-250	50/60	GP	6K	65	2/M	PP/-	-
	10	125-250	50/60	GP	6K				
	-	125-250	50/60	1/4hp	6K				
	-	125-250	50/60	1/2hp	6K				
A24 w w/o prefix letter									
	0.1	125	60	GP	6K	65	2/2	PP/-	-
A25 w w/o prefix letter									
	1	125	60	GP	6K	65	2/2	PP/-	-
	5	125-250	60	GP	6K				
	-	125-250	60	1/4hp	6K				
A26 w w/o prefix letter									
	1	125	60	GP	6K	65	2/2	PP/-	-
	10	125-250	60	GP	6K				
	-	125-250	60	1/2hp	6K				
A27 w w/o prefix letter									
	5	125-250	60	GP	6K	65	2/2	PP/-	-
	10	125-250	60	GP	6K				
	-	125-250	60	1/4hp	6K				
	-	125-250	60	1/2hp	6K				
A28 w w/o prefix letter									
	10	125-250	50/60	GP	6K	65	2/2	PP/-	-
	-	125-250	50/60	1/2hp	6K				
A29 w w/o prefix letter									
	10	125-250	50/60	GP	6K	65	1/2	-/-	-
	-	125-250	50/60	1/2hp	6K				
C10 f/b -31EA, -35EA, -36EA, -42A or -46A									

	0.1	24	DC	-	6K	55	M/M	PP/-	2
P41 or P4A1, f/b letters and/or numbers									
	3	125	60	GP	6K	55	M/M	PP/-	2
	2	250	60	GP	6K				
RR	10	125	60	1/4hp	6K	65	2/1	PP/-	-
	8	250	60	1/4hp	6K				
	10	125	60	GP	6K				
	8	250	60	GP	6K				
RS1 f/b additional suffix letters and numbers									
	16	250	60	GP	10K	85	M/M	-/-	-
RS2 f/b additional suffix letters and numbers									
	21	250	60	GP	10K	85	M/M	-/-	-
RS3A-A f/b additional suffix									
	16	125	60	GP	10K	65	2/1	PP/-	-
	8	250	60	GP	10K				
	6	30	DC	-	10K				
RS3A-B f/b additional suffix									
	16	125	60	GP	10K	65	1/1	-/-	-
	8	250	60	GP	10K				
	6	30	DC	-	10K				
RS3A-E f/b additional suffix									
	16	125	60	GP	10K	65	1/2	-/-	-
	8	250	60	GP	10K				
	6	30	DC	-	10K				
RS3B-A f/b additional suffix									
	0.1	250	60	GP	50K	65	2/1	PP/-	-
	0.3	30	DC	-	50K				
RS3B-B f/b additional suffix									
	0.1	250	60	GP	50K	65	1/1	-/-	-
	0.3	30	DC	-	50K				
RS3B-E f/b additional suffix									
	0.1	250	60	GP	50K	65	1/2	-/-	-
	0.3	30	DC	-	50K				
RS3C-A f/b additional suffix									
	6	30	DC	-	10K	65	2/1	PP/-	-
	16	125	60	GP	10K				
	8	250	60	GP	10K				
	0.1	250	60	GP	10K				
	0.3	30	DC	-	10K				
RS4A f/b additional suffix									
	0.3	250	60	GP	10K	65	2/1	PP/-	-
	0.3	30	DC	-	10K				
RS4B f/b additional suffix									