

Han-Modular Compact housing



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0301
Specification	Han-Modular Compact housing
HARTING eCatalogue	https://b2b.harting.com/09140010301

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® Compact
Type of hood/housing	Bulkhead mounted housing

Version

Locking type	Single locking lever
Size	Modular Compact

Technical characteristics

Stripping length	10 mm PE contact
Tightening torque	1 Nm PE screw
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 in locked position

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61984
CE	Yes

Commercial data

Packaging size	10
Net weight	50 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors