

**Product Line**

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)**
- M12 (B)
- M12 (D)
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (X)
- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



**MSAP-03PFFP-SF8002**

Operating Temperature: -40°C ~ +105°C  
 Transmission Speed: N/A  
 Shielded: Plastic, Non-shielded  
 Jacket Material: N/A  
 Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity

[Add to Cart](#) [Inquiry](#) [Heart](#)

Can't find? [Customize your part](#)

**Mating Pair & Accessories**

Connector Type  [Search](#)

M Series, CAP-WBBFSA1 -40°C ~ +105°C	M Series, CAP-WBBFSPC1 -40°C ~ +105°C	M Series, CAP-WBBFSA1 -40°C ~ +105°C	M Series, M12, A... MSAP-03BMMMA-... -40°C ~ +105°C	M Series, M12, A... MSAP-03BMMMA-... -40°C ~ +105°C	M Series, M12, A... MSAP-03BMMB-... -40°C ~ +105°C
- 0 +	- 0 +	- 0 +	- 0 +	- 0 +	- 0 +
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

[Add to Cart](#) [Inquiry](#)

Specifications	Download / CAD
Nominal Current <b>4A</b>	Connector Type <b>Receptacle</b>
Shielded <b>Plastic, Non-shielded</b>	No. of Contacts <b>03</b>
Connector Gender <b>Female</b>	Backshell <b>Hexagonal</b>
Mating Style <b>Screw Thread</b>	IP Rating <b>IP68</b>
Assembly Style <b>PCB 180°</b>	

[More Options](#)

**People Also Bought**

- MSAP-03PFFP-...
- RCP-5SPFFB-...
- M12A-06BFFM-...
- AB-CB04ML-CBBL-...
- ACB-06AFFM-SL7A03