


SylMirror SYLMIRROR LED FLUTE IP44 WW 0043235



Product features

- LED mirror/cabinet light with 6W total power consumption, 540 lumen, 144° beam angle, IP44, IK03, CRI 80, 3000K colour temperature, 25,000 hours average life time, 400 mm length, 2 year warranty. Flute shape.



PRODUCT OVERVIEW

IPC Code	0043235
Product name	SYLMIRROR LED FLUTE IP44 WW
Technology	LED
Housing	PC Polycarbonate
Mount	Wall surface mounted
Fixture rating	Enclosed
General application	Residential & Consumer
ETIM Class	EC002892
E-number FI	4170556
E-number SE	7505162
Fixture luminous flux (lm)	540
Luminaire efficacy (lm/W)	90
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Total power consumption (W)	6
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	No
Housing colour	Chrome
IP rating	IP44
IK rating	IK03
Product EAN number	5410288432359

DATA TABLE

General data

IPC Code	0043235
Product name	SYLMIRROR LED FLUTE IP44 WW
Technology	LED

SylMirror SYLMIRROR LED FLUTE IP44 WW 0043235

Housing	PC Polycarbonate
Mount	Wall surface mounted
Fixture rating	Enclosed
General application	Residential & Consumer
Operating temperature range (°C)	-10°C - 45°C
ETIM Class	EC002892
E-number FI	4170556
E-number SE	7505162

Optical data

Fixture luminous flux (lm)	540
Luminaire efficacy (lm/W)	90
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	6
Mains voltage (V)	220-240V~
Electrical protection	Class II
Control gear required	No
Control gear type	LED driver constant current
Dimmable	No
Drive current (mA)	25
Inrush Current (A)	5
Inrush Duration (µs)	150
Glow Wire Test (°C)	650
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	50
Max. Luminaires per 16A C Breaker	100

Lifetime data

Performance ambient temperature Tq (°C)	25
Lifespan - L70 B50	25000

Physical data


Housing colour	Chrome
IP rating	IP44
IK rating	IK03
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	400
Nominal Product Width (mm)	115
Nominal Product Height (mm)	43
Weight (kg)	0.101

SylMirror SYLMIRROR LED FLUTE IP44 WW 0043235


Packaging

Single packaging type	Carton
Product EAN number	5410288432359
Packaging single length / height (cm)	41.0
Packaging single width (cm)	13.0
Packaging single depth (cm)	6.5
DUN14 (outer)	15410288432356
Units per outer package	6
Packaging outer length / height (cm)	43.0
Packaging outer width (cm)	41.0
Packaging outer depth (cm)	15.5

PHOTOMETRY





TECHNICAL DRAWINGS




SylMirror SYLMIRROR LED FLUTE IP44 WW 0043235


SYLVANIA 0043235


 This luminaire contains built-in LED lamps

 } LED


The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built-in LED lamps

 } LED

The lamps cannot be changed in the luminaire.

SYLVANIA 0043235 

874/2012