




REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------



DG027 - 4.0 - XXP - 19 - 00A (H)  
 (Series No.) (Pitch) (Poles) (Single Pitch) (Color):9.(White)  
 (RoHS)  
 00A-(Standard)

NOTES1:

UL Standard  
 Current :9A

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 4.0mm, Poles : N=01~03P
- 5.Operating temperature:-40°C~+105°C
- 6.Undimensioned Tolerances:

Pitch range in mm			Nominal dimension range in mm					⊖	∇
TO	Over	Over	TO	Over	Over	Over	0.1/10		
6	6 TO 10	10 TO 24	30	30 TO 60	60 TO 100	100 TO 150	<		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2'	

7.RoHS Compliance

DETACHED LISTS	PART NO.: /		宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD	
	APPD: /	NAME: DG027-4.0-XXP-19-00A(H)		
	CHKD: /	TITLE: CUSTOMER DRAWING		REV: /
	DRFT: /	DRAWING NO.: /		DO: /
THIRD ANGLE PROJECTION		DRAWING NO.: / MM (INCH)	DO NOT SCALE DRAWING	SCALE: 1:1