







REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE



(0.5)



- NOTES1:
UL Standard
1. Rated voltage/current : 300V / 10A
2. Torque Value : M2 , 1.77Lb.in
3. Wire Range : 26~16AWG
- IEC Standard
1. Rated voltage/current : 130V / 10A
2. Torque Value : M2 , 0.2N.m
3. Wire Range : 0.5~1.0mm²
- NOTES2:
1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 3.5/3.81mm, Poles : N=02~24P
3. Stripping length : 4~5mm
4. Withstanding voltage : AC1250V/1Min
5. Operating temperature : -40C~+105C
6. Undimensioned tolerances:

Pitch range in mm	Nominal dimension range		mm	mm	mm	mm	mm	mm
	Over	Under						
TO	TO	TO	TO	TO	TO	TO	TO	TO
6	10	24	30	60	100	150	150	±2°
F0.15	F0.20	F0.30	F0.30	F0.50	F0.70	F1.00	F1.30	

7. RoHS Compliance

DG381 - 3.5/3.81 - XXP - 1Y - 00A (H)
(Series No.) (Pitch) (Poles) (Single Pitch) (Color):1.(Grey)
2.(Blue)
3.(Black)
4.(Green)
5.(Orange)
6.(Red)
7.(Transparent)
8.(Yellow)
9.(White)

DETACHED LISTS			
PART NO.:	/	NAME:	DEGSON [®] NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司
APPD:	/	CHKD:	/
DRFT:	/	TITLE:	CUSTOMER DRAWING
THIRD ANGLE PROJECTION		DRAWING NO.:	/
		DO NOT SCALE DRAWING	SCALE
			1:1

A B C D E F G H

A B C D E F G H

8 7 6 5 4 3 2 1