

Model	Center	Picture carrier (MHZ)	Color carrier	Sound carrier	Adjacent picture carrier	Adjacent sound carrier	Package	System	Remarks
D58M	57	58.75/-3.5±1.5	55.17/-3.5±1.5	54.25/-17.5±2.0	52.75/≤-43.0	60.25/≤-42.0	S-6BA	M.N	
F1332L		38					TO-5	D.K	
D36.9M	34,875	36.875/-4.5±1.5	32.445/-	31.375/-10.0±3.0	29.875/≤-42.0	38.375/≤-42.0	TO-5		
F1814D	36.9/5.0±1.0	38,9	34.47/3.0±1.5	33.4/≤-28.0	31.9/≤-38.0	40.0/≤-39.0	TO-8	B.G.D.K	
K2953M	36	38/-5.5±1.2	33.57/-1.0±1.2	31.5/-18.5±1.5; 32.0/-18.5±1.5	30.0/≤-44.0	39.5/≤-43.0	TO-5		
K2960M	36,9	38.9/-5.7±1.2	34.47/-1.5±1.2	32.4/-14.5±2.0; 33.4/-14.5±2.0	30.9/≤-43.0	40.4/≤-42.0	SF-915	D.K.B.G	
F5308		38,9					SF-915	B.G.I.D.	
N3804		38					TO-5	D.K	
K2955M	36,9	38.9/-6.5±1.2	34.47/-1.7±1.2	32.4/-19.5±2.0;33.4/-19.0±2.0	30.9/≤-44.0	40.4/≤-43.0;41.4/≤-	SF-915	B.G.D.K	
N38T14		38					TO-8	D.K	
N39.5		39,5					TO-5	H.I	
D1954	36	38/-4.5±1.0	33.57/-1.5±1.0	31.5/-15.0±2.0	30.0/≤-43.0	39.5/≤-42.0	TO-8	D.K	
D2967M	36	38/-5.0±1.5	33.57/-2.0±1.5	31.5/-18.5±1.5	30.0/≤-42.0	39.5/≤-42.0	TO-8		
D3832	32	38/≤-37.0	33.57/≤-30.0	31.5/1.5±1.0; 32.5/-0.2±1.0	30.0/≤-30.0	39.5/≤-35.0	T-4	B.G.D.I	
F1026S		38					TO-8	D.G.I	
N38-76	36	38/-4.5±1.0	33.57/0.3±1.0	31.5/-15.5±2.0; 32.5/-14.7±2.0	30.0/≤-45.0	39.5/≤-45.0	TO-8	D.K.B.G	
K9261		38	33.57/≤-22.0	31.5;32.0;32.15;32.5/-0.5±1.5	30.0/≤-32.0	39.5/≤-33.0	SF-915		
D38S		38					TO-8	D.K	
D1952		38					SIP5L	D.K	
N40.2		40,2					TO-5	B.G	
N3801A		38					TO-5	D.K	
F1357L	36	38/-4.7±1.5	33.57/-1.8±1.5	31.5/-13.7±1.2; 32.5/-12.1±2.0	30.0/≤-45.0	39.5/≤-45.0	TO-5	D.K.B.G	
D1954B	36	38/-4.8±1.5	33.57/-1.4±1.5	31.5/-20.0±2.0	30.0/≤-44.0	39.5/≤-42.0	TO-8	D.K.I	
K2966M	36,9	38.9/-6.0±1.5	34.47/-3.0±1.5	32.4/-20.0±2.0;33.4/-18.5±2.0	30.9/≤-45.0;31.9/≤-	40.4/≤-42.0;41.4/≤-	S-6BA	D.K.B.G	
D2952B	36,9	38.9/-4.5±1.5	34.47/-1.3±1.5	33.4/-20.0±3.0; 32.9/-15.6±3.0; 32.4/-21.5±3.0	31.9/≤-38.0	40.4/≤-41.0	TO-8	D.K.B.G	
SF1311							TO-8	H.I	
K3865N	36	38	33,57	31.5/-0.5±1.5; 32.5/-0.5±1.5	30.0/≤-30.0;	39.5/≤-30.0	T-4	D.K.B.G	
D45		45,75					SF-915	M.N	
N38-84		38					TO-5	D.K	
F1806E	32	38/≤-37.0	33.57/≤-22.0	31.5/-1.3±1.5; 32.5/1.5±1.5	30.0/≤-30.0	39.5/≤-32.0	T-4	B.G.D.I	