


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	PLY-13	NEMA 5-15P	1	black overmold
2	PLY-18	C13 female	1	black overmold
3	30-00244	Wire, 3C, 18 AWG, UL SVT, 300V, 105C, 6.3 mm, VW-1, PVC	1	
4	Label	Adhesive flag, 15x100 mm	1	white with black font




Wiring Diagram		PLY-18
PLY-13	wire color	PLY-18
hot	black	line
neutral	white	neutral
ground	green	ground

Notes:
Electrical requirements: 10 A at 125 Vac

Revision:	Date:	Description:	Prepared:	Notes:
A	12/20/2012	Initial release	JP Digitally signed by JP Date: 2018.08.21 14:32:17 -0700	RoHS compliant Function test: no open, no short circuit, no intermittent
			LA Digitally signed by LA Date: 2018.08.21 14:53:59 -0700	Description: Ac cord, 1000 mm, U.S. NEMA 5-15P plug, TLY-13 to C13, TLY-18, 18 AWG, SVT wire, 30-00244
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Size: Part number: A 11-00022
				Scale: 1:2

TENSILITY

tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com



Sheet 1 of 1