


OSMT Surface Mount Coaxial Connectors (Continued)


Right Angle Jack to Jack Cable Assembly 180° Offset



Cable Lengths	M/A-COM Model No.	Part No.
100 4.0	9950-3100-23	1064353-1
200 8.0	9950-3200-23	1064357-1
305 12.0	9950-3305-23	1064358-1

- Notes:
1. Consult AMP for non-standard cable lengths.
 2. Connector centerlines align $180^\circ \pm 30^\circ$ as shown.
 3. Cable length tolerance: 50.0 [1.97]-20000.0 [787.4]: $\pm (2.0 [0.08] + 1\%$ of cable length)

Right Angle Jack to Jack Cable Assembly



Cable Lengths	M/A-COM Model No.	Part No.
100 4.0	9950-1100-23	1064303-1
200 8.0	9950-1200-23	1064309-1
305 12.0	9950-1305-23	1064315-1

- Notes:
1. Connectors are randomly aligned.
 2. Consult AMP for non-standard cable lengths. Cable length tolerance: 50.0 [1.97]-20000.0 [787.4]: $\pm (2.0 [0.08] + 1\%$ of cable length)