




SPECIFICATION

Current Rating:1 Amp
 Voltage Rating:250V
 Dielectric Withstanding Voltage:500V AC RMS
 Contact Resistance:20 Milliohms Max.
 Insulation Resistance:5000 Megaohms Min.
 Operation Temperature:-55°C~+125°C
 Insulator:PBT+30%G.F.(UL94V-0)
 △ Contact:Brass,Gold Flash On Contact Area,
 Tin Plated On Solder Tails,Over Nickel
 Shell:Steel,Tin Plated On Back Shell
 Nickel Plated On Front Shell
 RoHS Compliant



- DS XX S T - XX - H
 (1) (2) (3) (4) (5) (6)
- (1) DS:D-SUB Solder Type
 - (2) XX:No. Of Position
 09:09 Position
 15:15 Position
 25:25 Position
 37:37 Position
 - (3) S:Female
 - (4) T:Tray
 - (5) XX:Insulator Color
 Blank:Blue
 BK:Black
 WH:White
 - (6) H:RoHS Compliant

Pin	A	B	C	D
09	30.80	24.99	16.33	19.28
15	39.20	33.32	24.66	27.65
25	53.10	47.04	38.35	41.20
37	69.40	63.50	54.80	57.44

AUK A MEMBER OF AUK GROUP
太聯事業股份有限公司
AUK CONTRACTORS CO., LTD.

CATEGORY		APPROVED BY EMILY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE X ±0.50 XX ±0.38 XXX ±0.25 ANG. ±2°
PART No. DSXXST-XX-H		CHECKED BY HZF		
DRAWING No. DSXXST-XX-H		DRAWING BY CYP		
SCALE	NONE	REV.	A2	
UNIT mm				

NO.	REV.	REVISIONS	CHK	DATE
△A2		Modify Dim.	HZF	06/15/2015
△A1		Modify Data	HZF	11/05/2014
△A0		NEW RELEASE	HZF	02/25/2010