




Recommended P.C.B. Layout

**SPECIFICATION**

Current Rating:1 Amp  
 Withstand Voltage:500V AC/Minute  
 Contact Resistance:20 Milliohms Max.  
 Insulation Resistance:1000 Megaohms Min.  
 Operation Temperature:-40°C~+105°C  
 ⚠ Housing:PA9T+30%G.F.(UL94V-0),Black  
 Contact:Brass,Gold Flash Over Nickel  
 RoHS Compliant

**HAB D XXX - H H**

- (1) (2) (3) (4)(5)
- (1) HAB:1.27X1.27mm Box Header
- (2) D:DIP Straight
- (3) XXX:No. Of Position
- (4) H:Withstand High Temperature Soldering
- (5) H:RoHS Compliant



Pin	A	B	C
6	10.11	8.56	2.54
10	12.65	11.10	5.08
12	13.92	12.37	6.35
14	15.19	13.64	7.62
16	16.46	14.91	8.89
20	19.00	17.45	11.43
24	21.54	19.99	13.97
26	22.81	21.26	15.24
28	24.08	22.53	16.51
30	25.35	23.80	17.78
34	27.89	26.34	20.32
40	31.70	30.15	24.13
44	34.24	32.69	26.67
50	38.05	36.50	30.48
60	44.40	42.85	36.83
64	46.94	45.39	39.37
68	49.48	47.93	41.91
80	57.10	55.55	49.53
100	69.80	68.25	62.23

**AUK** A MEMBER OF AUK GROUP  
**太聯事業股份有限公司**  
**AUK CONTRACTORS CO., LTD.**

CATEGORY		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE .X ±0.30 .XX ±0.20
PART No. HABDXXX-HH		MEI		
DRAWING No. HABDXXX-HH		CHECKED BY HZF		
SCALE NONE		DRAWING BY CYP		
REV.	A1	UNIT mm		

NO.	REV.	REVISIONS	CHK	DATE
⚠ A1		Modify Spec.	HZF	05/24/2017
⚠ A0		NEW RELEASE	HZF	09/16/2016