




SPECIFICATION

Current Rating:1.0A AC/DC
 Voltage Rating:125V AC/DC
 Contact Resistance:20 Milliohms Max.
 Withstanding Voltage:250V AC/Minute
 Insulation Resistance:100 Megaohms Min.
 Temperature Range:-25°C~+85°C
 Insulator:PA66(UL94V-0)
 RoHS Compliant

FH XX H - H
 (1) (2) (3) (4)

- (1) FH:1.25mm FH Series
- (2) XX:No. Of Position
- (3) H:Female Housing
- (4) H:RoHS Compliant



Pin	A	B
02	4.25	1.25
03	5.50	2.50
04	6.75	3.75
05	8.00	5.00
06	9.25	6.25
07	10.50	7.50
08	11.75	8.75
09	13.00	10.00
10	14.25	11.25
11	15.50	12.50
12	16.75	13.75
13	18.00	15.00
14	19.25	16.25
15	20.50	17.50

AUK A MEMBER OF AUK GROUP
太聯事業股份有限公司
AUK CONTRACTORS CO., LTD.

CATEGORY		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE X. ± 0.20 XX ± 0.13 XXX ± 0.08 .XXX ± 0.02 ANG. $\pm 1^\circ$
PART No. FHXXH-H		MEI		
DRAWING No. FHXXH-H		CHECKED BY HZF		
		DRAWING BY CYP		
SCALE	NONE	REV.	A0	UNIT mm

NO.	REV.	REVISIONS	CHK	DATE
△ A0		NEW RELEASE	HZF	12/30/2015