




European P.C.B. type terminal blocks / EK series



EHK750V



Pitch: 7.50mm

Approval	 	
Technical Data	UL	IEC
Rated voltage	300V	750V
Rated current	25A	24A
Conductor cross-section, solid (AWG/ mm ²)	24~12 / 0.5~2.5	
Conductor cross-section, flexible (AWG/ mm ²)	24~12 / 0.5~2.5	
Rated surge voltage (UL/IEC/Max.)	1.6 / 2.5 / KV	
Torque (N-m)	0.40	
Screw	M2.5	
Wire strip length	6~7mm	
Pole	Cat. No.	
02	EHK750V-02P	
03	EHK750V-03P	
:	:	
:	:	

TEL: +886-2-2908-0614

FAX: +886-2-2908-8549

E-mail: info@dinkle.com.tw