




△ SPECIFICATION
 Current Rating:3A AC/DC
 Voltage Rating:250V AC/DC
 Withstand Voltage:800V AC/Minute
 Insulation Resistance:1000 Megaohms Min.
 Temperature Range:-25°C~+85°C
 Material:PA66(UL94V-2),Black
 RoHS Compliant



Pin	A	B
4	2.00	6.00
6	4.00	8.00
8	6.00	10.00
10	8.00	12.00
12	10.00	14.00
14	12.00	16.00
16	14.00	18.00
18	16.00	20.00
20	18.00	22.00
22	20.00	24.00
24	22.00	26.00
26	24.00	28.00
28	26.00	30.00
30	28.00	32.00
32	30.00	34.00

AUK A MEMBER OF AUK GROUP
太聯事業股份有限公司
AUK CONTRACTORS CO., LTD.

CATEGORY		APPROVED BY MEI		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE △ .X ±0.38 .XX ±0.25 ANG.
PART No. DFEXXH-H		CHECKED BY HZF		
DRAWING No. DFEXXH-H		DRAWING BY WZL		
SCALE	NONE	REV.	A1	
UNIT mm				

NO.	REV.	REVISIONS	CHK	DATE
△ A1		Modify Data	HZF	09/23/2010
△ A0		NEW RELEASE		