





SPECIFICATIONS
 Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C To +85°C
 Contact Resistance: 10 Milliohms Max.
 Insulation Resistance: 500 Megohms Min.
 Withstanding Voltage: 1000V AC/Minute
 Pin Material: Brass, Tin Plated
 Material: PBT+15%GF, UL 94V-0



Circuits	Dim.A	Dim.B
02	5.08	2.54
03	7.62	5.08
04	10.16	7.62
05	12.70	10.16
06	15.24	12.70
07	17.78	15.24
08	20.32	17.78
09	22.86	20.32
10	25.40	22.86
11	27.94	25.40
12	30.48	27.94

AUK A MEMBER OF AUK GROUP
太聯事業股份有限公司
AUK CONTRACTORS CO., LTD.

CATEGORY		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ~3 ±0.10 3~10 ±0.15 10~20 ±0.20 20~30 ±0.25 30~ ±0.35 ANG. ±2°
PART No. MCGXXH		MEI		
DRAWING No. MCGXXH		CHECKED BY BECKY		
SCALE NONE		DRAWING BY TCF		
REV. A0		UNIT mm		

NO.	REV.	REVISIONS	CHK	DATE
△ A0		NEW RELEASE	BECKY	12/22/2004