

push-in fitting NPQM-DK-M5-Q4-P10

Part number: 558657

FESTO



Data sheet

| Feature | Value |
|-----------------------------------------------|---------------------------------------------------------|
| Size | Standard |
| Nominal size | 2.5 mm |
| Type of seal on screw-in stud | Sealing ring |
| Design structure | Push/pull principle |
| Operating pressure complete temperature range | -0.95 ... 16 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7::-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Ambient temperature | -20 ... 70 °C |
| Nominal tightening torque | 1 Nm |
| Tolerance for nominal tightening torque | ± 20 % |
| Product weight | 4.6 g |
| Pneumatic connection, port 1 | M5 |
| Pneumatic connection, port 2 | For tubing outside diameter 4 mm |
| Materials note | Conforms to RoHS |
| Material housing | Nickel-plated brass |
| Material of tubing seal | NBR |