





SPECIFICATION

- 1. **General Characteristics**
3.0mm Micro Fit 2XXX Plug Black
- 2. **Material&Finish**
Housing:PA66(UL94V-0),Black
- 3. **Electrical Characteristics**
Current Rating:3A AC/DC
Voltage Rating:250V AC/DC
Withstand Voltage:1500V AC/Minute
Insulation Resistance:1000 Megaohms Min.
- 4. **Environmental Characteristics**
Temperature Range:-25°C~+85°C
- 5. **RoHS Compliant**

MIF 2 X XX PH - H
 (1) (2) (3) (4) (5)

- (1) MIF:3.0 Micro-Fit Series
- (2) 2: Dual Row
- (3) XX: No. Of Position/Per Row
- (4) PH: Male Housing
- (5) H: RoHS Compliant



Dim. A,B Tolerance As Follow:

Pin	A	B
2~8	± 0.15	± 0.20
10~16	± 0.25	± 0.30
18~24	± 0.35	± 0.40

Pin	A	B
2	-	3.8
4	3.0	6.8
6	6.0	9.8
8	9.0	12.8
10	12.0	15.8
12	15.0	18.8
14	18.0	21.8
16	21.0	24.8
18	24.0	27.8
20	27.0	30.8
22	30.0	33.8
24	33.0	36.8

AUK A MEMBER OF AUK GROUP
太聯事業股份有限公司
AUK CONTRACTORS CO., LTD.

CATEGORY	APPROVED BY	MEI	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE $X_1 \pm 0.5$ $.XX \pm 0.25$ $.XXX \pm 0.08$
PART No. MIF2XXXPH-H	CHECKED BY	HZF	
DRAWING No. MIF2XXXPH-H	DRAWING BY	CYP	
SCALE	NONE	REV. A2	
UNIT	mm		

NO.	REV.	REVISIONS	CHK	DATE
A2		Modify Data	HZF	06/07/2017
A1		Modify Data	HZF	11/30/2009
A0		NEW RELEASE		