




REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 08/11/07'	~	LJC 08/11/07'
B	DRAWING UPDATE	JLZ 08/18/16'	~	



N=CONTACTS/2



RECOMMEND PCB LAYOUT(TOLERANCE=±0.05)

NOTES:

- MATERIAL
 - INSULATOR:THERMOPLASTIC(UL 94V-0).
 - CONTACT MATERIAL:COPPER ALLOY.
- SPECIFICATION
 - CURRENT RATING:1.0 Amp.
 - INSULATION RESISTANCE:500MΩ Min.
 - DIELECTRIC WITHSTANDING:300VAC.
 - CONTACT RESISTANCE:20mΩ Max.
 - OPERATING TEMPERATURE:-40°C TO+105°C.

3. PRODUCT NUMBER CODE:


DS1031-06 - X X X X X X - X

- PLATING LEVEL
3A: LEVEL 3A
- DIM.A B TYPE
1: TYPE 1
2: TYPE 2
OR A*/B*.*
- HOUSING DIM(DIM. C)
1: 1.00mm
2: 1.50mm
3: 1.70mm
4: 2.00mm
5: 2.50mm
- MOUNTING TYPE
V: VERTICAL TYPE
- HOUSING COLOR
B:BLACK
- CONTACT PLATING
8: FULL GOLD FLASH
- CONNECTOR TYPE
P:PLUG
- No.OF CONTACTS
2*2-2*40

TYPE	DIM A	DIM B
1	3.70	2.10
2	3.50	3.50
3	4.00	2.50
4	3.00	2.30
5	2.50	2.00
6	3.30	2.50
7		
8		
9		

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°
DRAWING TYPE		CUSTOMER	
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1031-06-XXXXXX-X-B		

PROJECTION	TITLE
UNITS	1.27mm PITCH PIN HEADER DUAL ROW STRAIGHT
SHEET SIZE	SERIES DS1031-06 SERIES

 晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO., LTD

Tel:86-574-63508787

Fax:86-574-63510817

E-mail:sale@connfly.com

http://www.connfly.com

Add:East Industry Zone KuangYan

Town Cixi Ningbo China

P.C:315333