



PCB LAYOUT
RECOMMEND PCB THICKNESS: 1.57 mm

Specification
 . Current Rating: 5A AC/DC
 . Voltage Rating: 250V AC
 ⚠ Temperature Range: -40°C~+85°C
 . Contact Resistance: 50 Milliohms Max.
 . Insulation Resistance: 1000 Megohms Min.
 ⚠ Dielectrical Withstanding Voltage: 1500V AC R.M.S. Min. for 1 minute

. Contact: Copper Alloy, Tin Plated
 . Insulator Material: PBT, UL94V-0 ,Color: Black
 . RoHS Compliant
 . Part No:
 MIF 2 X XX P R P -H
 ① ② ③ ④ ⑤ ⑥

- ① MIF: Micro Fit
- ② 2: Double Row
- ③ XX: No.Of Pin Per Row, 1~12 Pins
- ④ P: Male
- ⑤ R: Dip 90°
- ⑥ P: W/ Post, Plastic Mounting Peg

Position	Dim A	Dim B	Dim C
2	— —	6.0	— —
4	3.00	9.0	— —
6	6.00	12.0	— —
8	9.00	15.0	4.70
10	12.00	18.0	7.70
12	15.00	21.0	10.70
14	18.00	24.0	13.70
16	21.00	27.0	16.70
18	24.00	30.0	19.70
20	27.00	33.0	22.70
22	30.00	36.0	25.70
24	33.00	39.0	28.70

CATEGORY WAFER		APPROVED BY VIVIAN		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE .X ±0.38 .XX ±0.25 ANG. ±1°
PART No. MIF2XXXPRP-H		CHECKED BY LYS		
DRAWING No. MIF2XXXPRP-H		DRAWING BY SJH		
SCALE NONE	REV. A2	UNIT mm		

NO.	REV.	REVISIONS	CHK	DATE
△ A2		MARKED △ WERE AREA CHANGED	SJH	06/26/2014
△ A1		MODIFY DWV	TONY	09/21/2006
△ A0		NEW RELEASE	TONY	03/28/2005