




△ SPECIFICATION
 Current Rating:2A AC/DC
 Voltage Rating:250V AC/DC
 Withstanding Voltage:800V AC/Minute
 Insulation Resistance:1000 Megaohms Min.
 Contact Resistance:20 Milliohms Max.
 Temperature Range:-25°C~+85°C
 Insulator:PA66(UL94V-0)
 RoHS Compliant



△

Pin	A	B
04	2.0	5.9
06	4.0	7.9
08	6.0	9.9
10	8.0	11.9
12	10.0	13.9
14	12.0	15.9
16	14.0	17.9
18	16.0	19.9
20	18.0	21.9
22	20.0	23.9
24	22.0	25.9
26	24.0	27.9
28	26.0	29.9
30	28.0	31.9
32	30.0	33.9
34	32.0	35.9
40	38.0	41.90

AUK A MEMBER OF AUK GROUP
太聯事業股份有限公司
AUK CONTRACTORS CO., LTD.

CATEGORY		APPROVED BY EMILY	
PART No. PHDXXH-H		CHECKED BY HZF	
DRAWING No. PHDXXH-H		DRAWING BY SONG	
SCALE	NONE	REV.	A1

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
 △ .X ±0.35
 .XX ±0.25
 ANG.

UNIT mm

NO.	REV.	REVISIONS	CHK	DATE
△ A1		Modify Data	HZF	12/22/2012
△ A0		NEW RELEASE		