




Recommended P.C.B. Layout

△ SPECIFICATION
 Current Rating: 2A AC/DC
 Voltage Rating: 250V AC/DC
 Operation Temperature: -25°C~+85°C
 Contact Resistance: 20 Milliohms Max.
 Insulation Resistance: 1000 Megaohms Min.
 Terminal: Brass, Tin Plated
 Material: PA66+G.F.(UL94V-0)
 RoHS Compliant



Pos.	A	B
4	2.0	6.0
6	4.0	8.0
8	6.0	10.0
10	8.0	12.0
12	10.0	14.0
14	12.0	16.0
16	14.0	18.0
18	16.0	20.0
20	18.0	22.0
22	20.0	24.0
24	22.0	26.0
26	24.0	28.0
28	26.0	30.0
30	28.0	32.0
32	30.0	34.0
34	32.0	36.0
40	38.0	42.0



AUK A MEMBER OF AUK GROUP
太聯事業股份有限公司
AUK CONTRACTORS CO., LTD.

CATEGORY		APPROVED BY MEI		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE △ .X ±0.35 .XX ±0.25 UNIT mm
PART No. PHDXXR-H		CHECKED BY HZF		
DRAWING No. PHDXXR-H		DRAWING BY WZL		
SCALE	NONE	REV.	A2	

NO.	REV.	REVISIONS	CHK	DATE
△ A2		Modify Data	HZF	02/23/2010
△ A1		Modify Data	INGRID	03/28/2008
△ A0		NEW RELEASE		