


REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 03/16/12'	~	LJC 03/16/12'
B	DRAWING UPDATE	JLZ 03/23/17'	~	



NOTES:

- SPECIFICATIONS:
 - CONTACT RESISTANCE: 30mΩ max.
 - INSULATOR RESISTANCE: 1000MΩ min. AT DC 500V.
 - CURRENT RATING: 1.5A.
 - VOLTAGE RATING: 30VDC.
 - DIELECTRIC STRENGTH: AC 500V FOR 1 Minute.
- MATERIALS:
 - HOUSING: THERMOPLASTIC (UL 94 V-0).
 - CONTACT: COPPER ALLOY
 - SHELL: COPPER ALLOY
- ENVIRONMENT CHARACTERISTICS:
 - TEMPERATURE: -20°C ~ +85°C.

4. PRODUCT NUMBER CODE:

DS1096-01 - X X X

- CONTACT Plating
 - 0: Selective Gold flash
 - 03: Selective Gold 3u"
 - 30: Selective Gold 30u"
- SHELL Plating
 - N: Nickel
- COLOR OF HOUSING:
 - W: WHITE
 - B: BLACK
 - L: BLUE
- PRODUCTS SERIES: DS1096-01

Tel: 86-574-6350787
 Fax: 86-574-63510817
 E-mail: sales@connfly.com
 http://www.connfly.com
 Add: East Industry Zone KuangYan
 Town Cixi Ningbo City
 P.C: 315333

RECOMMEND PCB LAYOUT
 TOLERANCE = ±0.05

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE	USB 3.0 STACK 18 PIN FEMALE RIGHT ANGLE TYPE	
X.	±0.60	X.	±5°	mm			
.X	±0.38	.X	±3°	A4	SERIES	DS1096-01 SERIES	
.XX	±0.25	.XX	±2°				
DRAWING TYPE		CUSTOMER		晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD			
SCALE		1:1 SHEET 1 OF 1					
DRAWING NO.		C-DS1096-01-XXX-B					