

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	JLZ 10/07/14'		LJC 10/07/14'
B	ARRANGEMENT DRAWING	JLZ 11/06/15'		

Notes:

1.Material:

- 1.1. Housing: High Temperature LCP UL 94V-0 Color: Black.
- 2.1. 2. Contacts: Copper Alloy. Selective Gold Flash.

2.Specifications:

- 2.1. Operate Temperature:  $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 2.2. Insulation Resistance:  $1000\text{M}\Omega$  Min.
- 2.3. Contact Resistance:  $50\text{m}\Omega$  max.
- 2.4. Withstanding Voltage:  $500\text{V AC 1min.}$
- 2.5. Voltage Rating:  $30\text{V AC/DC}$
- 2.6. Current Rating:  $1.0\text{A}$

3.Product Number Code:

DS1138-02 - XX X X X X 0 X

Packing Type  
R: Tape On Reel  
B: Tube


Housing color  
B: Black

Contact Plating  
4: Selective  $3\mu$  gold

Mounting type  
S: SMT type

Connector type  
S: Socket

No. of contacts  
06:6pin



GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	$\pm 0.60$	X.	$\pm 5^{\circ}$
.X	$\pm 0.38$	.X	$\pm 3^{\circ}$
.XX	$\pm 0.25$	.XX	$\pm 2^{\circ}$

PROJECTION	TITLE	2.54mm SIM Card H=2.6mm 6 Positions SMT Type	
		SHEET SIZE	A4
UNITS	mm	SERIES	DS1138-02 SERIES

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1138-02-XXXXXXX-B		

晨翔电子有限公司  
**CONNFLY® CONNFLY ELECTRONIC CO., LTD**