

.

1.25mm Pitch Miniature Crimping Connector

DF13 Series





■Features

1. Miniature Size

Designed in the low profile at mounting height 5.8mm. (SMT mounting straight type)

(For DIP type, the mounting height is to 5.3mm to the straight and 3.6mm at the right angle)

2. Multi-contact

The double row type achieves the multi-contact up to 40 contacts, and secures 30% higher density in the mounting area, compared with the single row type.

3. Correspond to Automatic Mounting

The header provides the grade with the vacuum absorption area, and secures automatic mounting by the embossed tape packaging.

In addition, the tube packaging can be selected.


4. Integral Basic Function Despite Miniature Size

The header is designed in a scoop-proof box structure, and completely prevents mis-insertion.

In addition, the surface mounting (SMT) header is equipped with the metal fitting to prevent solder peeling.

■Applications

Note PC, mobile terminal, miniature type business equipment, and other various consumer equipment, including video camera



■Product Specifications

Rating	Current rating 1A		Operating Temperature Range: -35 to +85°C (Note 1)	Storage Temperature Range: -10 to +60℃	(Note 2)
raung	Voltage rating 150V	'AC	Operating Moisture Range: 40 to 80%	Storage Moisture Range: 40 to 70%	(Note 2)

Item	Specification	Condition
1.Insulation Resistance	500M ohms min.	100V DC
2.Withstanding voltage	No flashover or insulation breakdown.	500V AC/1 minute
3.Contact Resistance	30m ohms max.	100mA
4.Single Insertion/Extraction Force	0.3N (30gf) min., 3N (300gf) max.	Measured at the square steel pin of 0.35±0.002mm
5.Vibration	No electrical discontinuity of 1 μ s or more	Frequency: 10 to 55 Hz, single amplitude of 0.75 mm, 2 hours in each of the 3 directions.
6.Humidity (Steady state)	Contact resistance: 30m ohms max. Insulation resistance: 500M ohms min.	96 hours at temperature of 40°C and humidity of 90% to 95%
7.Temperature Cycle	Contact resistance: 30m ohms max. Insulation resistance: 500M ohms min.	(-55°C: 30 minutes→ 5 to 35°C: 10 minutes→ 85°C: 30 minutes→ 5 to 35°C: 10 minutes) 5 cycles
8.Durability (Mating/un-mating)	Contact resistance: 30m ohms max.	Tin plating: 30 cycles
		Gold plating: 50 cycles
9.Resistance to Soldering heat	No deformation of components affecting performance.	Flow: 250°C for 10 seconds
		Manual soldering: 300℃ for 3 seconds
		Reflow: At the recommended temperature profile
		Manual soldering: 300℃ for 3 seconds

Note 1: Includes temperature rise caused by current flow.

Note 2: The term "storage" refers to products stored for long period of time prior to mounting and use. Operating Temperature Range and Humidity range covers non conducting condition of installed connectors in storage, shipment or during transportation.

■Material

Product	Part	Material	Finish	Remarks
Crimping Socket	g Socket Insulator Polyamide		Beige	UL94V-0
Crimping Contact for Socket	Contact	Phosphor copper	Tin plated or gold plated	
Die Heeder (Theoret hele)	Insulator	Polyamide	Beige	UL94V-0
Pin Header (Through hole)	Contact	Brass	Tin plated	
	Insulator	Polyamide	Beige	UL94V-0
Pin Header (SMT)	Contact	Brass	Tin plated or gold plated	
	Metal Fitting	Phosphor copper	Tin plated	

■Ordering Information

Connector


Series Name	: DF13	3 Number of Contacts	5 Contact Pitch: 1.25mm
Style Symbol	: Blank: With boss	Single row: 2 to 12, 14, 15	6 Contact Type
	A: Without boss	Double row: 10, 20, 30, 40	C : Crimping socket / DSA : Straight through hole
V Type —	— B: With boss, embossed tape type	4 Connector Type	DS: Right angle through hole / V: Straight SMT
	— C: Without boss, embossed tape type	S: Single row socket / P: Single row pin header	H : Right angle SMT
		DS: Double row socket / DP: Double row pin header	

●Contact

DF 13 -
$$\frac{2630}{0} \frac{\text{SCF}}{0} \frac{\text{A}}{6}$$

Applicable Cable Size 2630: AWG26 to 30	3 Plating Type	Blank: Tin plated
2 Packaging Type SCF: Socket Contact/Reel		A : Gold plated

■Single Row Socket




Unit: mm

Part Number	CL No.	Number of Contacts	Α	В	Part Number	CL No.	Number of Contacts	Α	В
DF13-2S-1.25C(**)	536-0001-4-**	2	1.25	4.15	DF13- 9S-1.25C(**)	536-0008-3-**	9	10.00	12.90
DF13-3S-1.25C(**)	536-0002-7-**	3	2.50	5.40	DF13-10S-1.25C(**)	536-0009-6-**	10	11.25	14.15
DF13-4S-1.25C(**)	536-0003-0-**	4	3.75	6.65	DF13-11S-1.25C(**)	536-0010-5-**	11	12.50	15.40
DF13-5S-1.25C(**)	536-0004-2-**	5	5.00	7.90	DF13-12S-1.25C(**)	536-0011-8-**	12	13.75	16.65
DF13-6S-1.25C(**)	536-0005-5-**	6	6.25	9.15	DF13-14S-1.25C(**)	536-0013-3-**	14	16.25	19.15
DF13-7S-1.25C(**)	536-0006-8-**	7	7.50	10.40	DF13-15S-1.25C(**)	536-0014-6-**	15	17.50	20.40
DF13-8S-1.25C(**)	536-0007-0-**	8	8.75	11.65					

Note 1.The quantity at the specific No. "None" is delivered per bag (100 pcs.). If needed, please select and order the products per bag.

■Double Row Socket




Part Number	CL No.	Number of Contacts	Α	В
DF13-10DS-1.25C(**)	536-0550-2-**	10	10.40	5.00
DF13-20DS-1.25C(**)	536-0555-6-**	20	16.65	11.25
DF13-30DS-1.25C(**)	536-0560-6-**	30	22.90	17.50
DF13-40DS-1.25C(**)	536-0565-0-**	40	29.15	23.75


[Specific No.] – **, (**) Blank: 1 bag: 100 pcs.


Note: The quantity at the specific No. "Blank" is delivered per bag (100pcs). If needed, please select and order the products per bag.

■Single Row Straight Pin Header (Through hole)




◆Board Through-hole Diameter: \$\phi 0.6\pm 0.03





[Specific No.] - **, (**) Blank: Tin plated 20: Tin plated, tube packaging



Unit: mm


Part Number	CL No.	Number of Contacts	Α	В	Part Number	CL No.	Number of Contacts	Α	В
DF13-2P-1.25DSA(**)	536-0101-9-**	2	1.25	4.15	DF13- 9P-1.25DSA(**)	536-0108-8-**	9	10.00	12.90
DF13-3P-1.25DSA(**)	536-0102-1-**	3	2.50	5.40	DF13-10P-1.25DSA(**)	536-0109-0-**	10	11.25	14.15
DF13-4P-1.25DSA(**)	536-0103-4-**	4	3.75	6.65	DF13-11P-1.25DSA(**)	536-0110-0-**	11	12.50	15.40
DF13-5P-1.25DSA(**)	536-0104-7-**	5	5.00	7.90	DF13-12P-1.25DSA(**)	536-0111-2-**	12	13.75	16.65
DF13-6P-1.25DSA(**)	536-0105-0-**	6	6.25	9.15	DF13-13P-1.25DSA(**)	536-0112-5-**	13	15.00	17.90
DF13-7P-1.25DSA(**)	536-0106-2-**	7	7.50	10.40	DF13-14P-1.25DSA(**)	536-0113-8-**	14	16.25	19.15
DF13-8P-1.25DSA(**)	536-0107-5-**	8	8.75	11.65	DF13-15P-1.25DSA(**)	536-0114-0-**	15	17.50	20.40

Note 1.The quantity at the specific No. "None" is delivered per bag (100 pcs.). If needed, please select and order the products per bag.


■Single Row Right Angle Pin Header (Through hole)



●Board Through-hole Diameter: ϕ 0.6 \pm 0.03



[Specific No.] - **, (***) (20): Tin plated tube packaging





Unit: mm

Part Number	CL No.	Number of Contacts	Α	В	Tube Packaging Quantity	Part Number	CL No.	Number of Contacts	Α	В	Tube Packaging Quantity
DF13-2P-1.25DS(**)	536-0151-7-**	2	1.25	4.15	115	DF13- 9P-1.25DS(**)	536-0158-6-**	9	10.00	12.90	37
DF13-3P-1.25DS(**)	536-0152-0-**	3	2.50	5.40	89	DF13-10P-1.25DS(**)	536-0159-9-**	10	11.25	14.15	34
DF13-4P-1.25DS(**)	536-0153-2-**	4	3.75	6.65	72	DF13-11P-1.25DS(**)	536-0160-8-**	11	12.50	15.40	31
DF13-5P-1.25DS(**)	536-0154-5-**	5	5.00	7.90	61	DF13-12P-1.25DS(**)	536-0161-0-**	12	13.75	16.65	29
DF13-6P-1.25DS(**)	536-0155-8-**	6	6.25	9.15	52	DF13-14P-1.25DS(**)	536-0163-6-**	14	16.25	19.15	25
DF13-7P-1.25DS(**)	536-0156-0-**	7	7.50	10.40	46	DF13-15P-1.25DS(**)	536-0164-9-**	15	17.50	20.40	23
DF13-8P-1.25DS(**)	536-0157-3-**	8	8.75	11.65	41						


Note 1.Order the tube packaging product, multiplying the tube packaging quantity.


● Single Row Straight Pin Header (SMT)





[Specific No.] – **, (**) (20): Tin plated tube package (50): Gold plated tube package






Unit: mm


Part Number	CL No.	Number of Contacts	Α	В	С	D	Е	F	Tube Package Quantity	Remark
DF13- 2P-1.25V(**)	536-0201-3-**	2	1.25	4.15	7.15	3.35	5.65	1.95	67	
DF13- 3P-1.25V(**)	536-0202-6-**	3	2.50	5.40	8.40	4.60	6.90	3.20	57	
DF13- 4P-1.25V(**)	536-0203-9-**	4	3.75	6.65	9.65	5.85	8.15	4.45	49	
DF13- 5P-1.25V(**)	536-0204-1-**	5	5.00	7.90	10.90	7.10	9.40	5.70	44	
DF13- 6P-1.25V(**)	536-0205-4-**	6	6.25	9.15	12.15	8.35	10.65	6.95	39	
DF13- 7P-1.25V(**)	536-0206-7-**	7	7.50	10.40	13.40	9.60	11.90	8.20	36	
DF13- 8P-1.25V(**)	536-0207-0-**	8	8.75	11.65	14.65	10.85	13.15	9.45	33	Guide post
DF13- 9P-1.25V(**)	536-0208-2-**	9	10.00	12.90	15.90	12.10	14.40	10.70	30	
DF13-10P-1.25V(**)	536-0209-5-**	10	11.25	14.15	17.15	13.35	15.65	11.95	28	
DF13-11P-1.25V(**)	536-0210-4-**	11	12.50	15.40	18.40	14.60	16.90	13.20	26	
DF13-12P-1.25V(**)	536-0211-7-**	12	13.75	16.65	19.65	15.85	18.15	14.45	24	
DF13-14P-1.25V(**)	536-0213-2-**	14	16.25	19.15	22.15	18.35	20.65	16.95	21	
DF13-15P-1.25V(**)	536-0214-5-**	15	17.50	20.40	23.40	19.60	21.90	18.20	20	

Note:Please order the tube packaging products, multiplying the tube packaging quantity.

●PCB mounting pattern

● Tube Dimensions





Note:If the pattern exists in the shaded area, and isn't treated with resist, it could touch the connector contact.

■Single Row Straight Pin Header (SMT)


(Three-Wall/Correspond to Vacuum Absorption)



Polarity mark 0.35×0.35

Note: "No guide post" indicates the style with no boss.

●PCB mounting pattern



Note 1. This hole isn't needed for "No guide post". Note 2.If the pattern exists in the shaded area, and isn't treated with resist, it could touch the connector contact.

[Specific No.] - **, (**)

(20): Tin plated tube packaging

(21): Tin plated embossed tape packaging

(50): Gold plated tube packaging

(51): Gold plated embossed tape packaging

Unit: mm


Part Number	CL No.	Number of Contacts	А	В	С	D	E	F	G	Tube Packaging Quantity	Emboss Width	Remarks
DF13B- 2P-1.25V(**)	536-0051-2-**	2	1.25	4.15	7.15	3.35	5.65	1.95	2.20	67pcs	16	
DF13B- 3P-1.25V(**)	536-0052-5-**	3	2.50	5.40	8.40	4.60	6.90	3.20	3.45	57	16	
DF13B- 4P-1.25V(**)	536-0053-8-**	4	3.75	6.65	9.65	5.85	8.15	4.45	3.10	49	24	
DF13B- 5P-1.25V(**)	536-0054-0-**	5	5.00	7.90	10.90	7.10	9.40	5.70	4.35	44	24	
DF13B- 6P-1.25V(**)	536-0055-3-**	6	6.25	9.15	12.15	8.35	10.65	6.95	5.60	39	24	
DF13B- 7P-1.25V(**)	536-0056-6-**	7	7.50	10.40	13.40	9.60	11.90	8.20	6.85	36	24	With
DF13B- 8P-1.25V(**)	536-0057-9-**	8	8.75	11.65	14.65	10.85	13.15	9.45	8.10	33	24	
DF13B- 9P-1.25V(**)	536-0058-1-**	9	10.00	12.90	15.90	12.10	14.40	10.70	9.35	30	24	boss
DF13B-10P-1.25V(**)	536-0059-4-**	10	11.25	14.15	17.15	13.35	15.65	11.95	10.60	28	24	
DF13B-11P-1.25V(**)	536-0060-3-**	11	12.50	15.40	18.40	14.60	16.90	13.20	11.85	26	32	
DF13B-12P-1.25V(**)	536-0061-6-**	12	13.75	16.65	19.65	15.85	18.15	14.45	13.10	24	32	
DF13B-14P-1.25V(**)	536-0063-1-**	14	16.25	19.15	22.15	18.35	20.65	16.95	15.60	21	32	
DF13B-15P-1.25V(**)	536-0064-4-**	15	17.50	20.40	23.40	19.60	21.90	18.20	16.85	20	44	
DF13C- 2P-1.25V(**)	536-0401-2-**	2	1.25	4.15	7.15	_	5.65	1.95	2.20	67pcs	16	
DF13C- 3P-1.25V(**)	536-0402-5-**	3	2.50	5.40	8.40	_	6.90	3.20	3.45	57	16	
DF13C- 4P-1.25V(**)	536-0403-8-**	4	3.75	6.65	9.65	_	8.15	4.45	3.10	49	24	
DF13C- 5P-1.25V(**)	536-0404-0-**	5	5.00	7.90	10.90	-	9.40	5.70	4.35	44	24	
DF13C- 6P-1.25V(**)	536-0405-3-**	6	6.25	9.15	12.15	_	10.65	6.95	5.60	39	24	
DF13C- 7P-1.25V(**)	536-0406-6-**	7	7.50	10.40	13.40	_	11.90	8.20	6.85	36	24	Without
DF13C- 8P-1.25V(**)	536-0407-9-**	8	8.75	11.65	14.65	_	13.15	9.45	8.10	33	24	
DF13C- 9P-1.25V(**)	536-0408-1-**	9	10.00	12.90	15.90	-	14.40	10.70	9.35	30	24	boss
DF13C-10P-1.25V(**)	536-0409-4-**	10	11.25	14.15	17.15	_	15.65	11.95	10.60	28	24	
DF13C-11P-1.25V(**)	536-0410-3-**	11	12.50	15.40	18.40	_	16.90	13.20	11.85	26	32	
DF13C-12P-1.25V(**)	536-0411-6-**	12	13.75	16.65	19.65	_	18.15	14.45	13.10	24	32	
DF13C-14P-1.25V(**)	536-0413-1-**	14	16.25	19.15	22.15	-	20.65	16.95	15.60	21	32	
DF13C-15P-1.25V(**)	536-0414-4-**	15	17.50	20.40	23.40	_	21.90	18.20	16.85	20	44	

Note 1.Please order the tube packaging product, multiplying the tube packaging quantity.

Note 2.Please order the embossed tape packaging product according to reel number. (1000 pcs. per reel)

■Single Row Right Angle Pin Header (SMT)


(Four-Wall/Correspond to Emboss Absorption)



◆Tube Dimensions

6.6 ω œ.

●PCB mounting pattern



Guide pos

Note: "without boss" indicates the style with no boss.

Note This hole isn't needed for "No guide post".

[Specific No.] - **, (**)

(20): Tin plated tube packaging

(21): Tin plated embossed tape packaging

(50): Gold plated tube packaging

(51): Gold plated embossed tape packaging

Unit: mm

										Unit: mm
Part Number	CL No.	Number of Contacts	А	В	С	D	Е	Tube Packaging Quantity	Emboss Width	Remarks
DF13- 2P-1.25H(**)	536-0251-1-**	2	1.25	4.15	7.15	3.35	5.65	67pcs	16	
DF13- 3P-1.25H(**)	536-0252-4-**	3	2.50	5.40	8.40	4.60	6.90	57	16	
DF13- 4P-1.25H(**)	536-0253-7-**	4	3.75	6.65	9.65	5.85	8.15	49	24	
DF13- 5P-1.25H(**)	536-0254-0-**	5	5.00	7.90	10.90	7.10	9.40	44	24	
DF13- 6P-1.25H(**)	536-0255-2-**	6	6.25	9.15	12.15	8.35	10.65	39	24	
DF13- 7P-1.25H(**)	536-0256-5-**	7	7.50	10.40	13.40	9.60	11.90	36	24	With
DF13- 8P-1.25H(**)	536-0257-8-**	8	8.75	11.65	14.65	10.85	13.15	33	24	
DF13- 9P-1.25H(**)	536-0258-0-**	9	10.00	12.90	15.90	12.10	14.40	30	24	boss
DF13-10P-1.25H(**)	536-0259-3-**	10	11.25	14.15	17.15	13.35	15.65	28	24	
DF13-11P-1.25H(**)	536-0260-2-**	11	12.50	15.40	18.40	14.60	16.90	26	32	
DF13-12P-1.25H(**)	536-0261-5-**	12	13.75	16.65	19.65	15.85	18.15	24	32	
DF13-14P-1.25H(**)	536-0263-0-**	14	16.25	19.15	22.15	18.35	20.65	21	32	
DF13-15P-1.25H(**)	536-0264-3-**	15	17.50	20.40	23.40	19.60	21.90	20	44	
DF13A- 2P-1.25H(**)	536-0301-8-**	2	1.25	4.15	7.15	_	5.65	67pcs	16	
DF13A- 3P-1.25H(**)	536-0302-0-**	3	2.50	5.40	8.40	_	6.90	57	16	
DF13A- 4P-1.25H(**)	536-0303-3-**	4	3.75	6.65	9.65	_	8.15	49	24	
DF13A- 5P-1.25H(**)	536-0304-6-**	5	5.00	7.90	10.90	_	9.40	44	24	
DF13A- 6P-1.25H(**)	536-0305-9-**	6	6.25	9.15	12.15	_	10.65	39	24	
DF13A- 7P-1.25H(**)	536-0306-1-**	7	7.50	10.40	13.40	_	11.90	36	24	Without
DF13A- 8P-1.25H(**)	536-0307-4-**	8	8.75	11.65	14.65	_	13.15	33	24	
DF13A- 9P-1.25H(**)	536-0308-7-**	9	10.00	12.90	15.90	_	14.40	30	24	boss
DF13A-10P-1.25H(**)	536-0309-0-**	10	11.25	14.15	17.15	_	15.65	28	24	
DF13A-11P-1.25H(**)	536-0310-9-**	11	12.50	15.40	18.40	_	16.90	26	32	
DF13A-12P-1.25H(**)	536-0311-1-**	12	13.75	16.65	19.65	_	18.15	24	32	
DF13A-14P-1.25H(**)	536-0313-7-**	14	16.25	19.15	22.15	_	20.65	21	32	
DF13A-15P-1.25H(**)	536-0314-0-**	15	17.50	20.40	23.40	_	21.90	20	44	


Note 1.Please order the tube packaging product, multiplying the tube packaging quantity.


Note 2.Please order the embossed tape packaging product according to reel number. (1000 pcs. per reel)

■Double Row Straight Pin Header (SMT)

(Four-Wall Type Compliant to Emboss Absorption)








Boss (Note)

Note:" Without boss" indicates the style with no boss.


● PCB mounting pattern



Note 1.If the pattern exists in the shaded area, and isn't treated with resist, it could touch the connector contact.

Note 2. The hole isn't needed at "Without boss".

◆Tube Dimensions



[Specific No.] - **, (**)

(20): Tin plated tube packaging

(29): Tin plated embossed tape packaging

(50): Gold plated tube packaging

(59): Gold plated embossed tape packaging

Unit: mm


Part Number	CL No.	Number of		В	С	D	Specification	Specification	Specification	Specification	Tube Package	Emboss	Remarks
Fait Number CL No.	Contacts	A	A B		ן ט	(20)	(29)	(50)	(59)	Quantity	Width	Remaiks	
DF13 -10DP-1.25V(**)	536-0510-8-**	10	12.1	5	8.7	7.5	0	0	0	0	40 pcs	24	
DF13 -20DP-1.25V(**)	536-0515-1-**	20	18.35	11.25	14.95	13.75	0	0	0	0	26	32	With
DF13 -30DP-1.25V(**)	536-0520-1-**	30	24.6	17.5	21.2	20	_	_	0	0	19	44	boss
DF13 -40DP-1.25V(**)	536-0525-5-**	40	30.85	23.75	27.45	26.25	_	_	0	0	15	44	
DF13A-10DP-1.25V(**)	536-0600-9-**	10	12.1	5	8.7	_	0	0	0	0	40	24	
DF13A-20DP-1.25V(**)	536-0605-2-**	20	18.35	11.25	14.95	_	0	0	0	0	26	32	Without
DF13A-30DP-1.25V(**)	536-0610-2-**	30	24.6	17.5	21.2	_	_	_	0	0	19	44	boss
DF13A-40DP-1.25V(**)	536-0615-6-**	40	30.85	23.75	27.45	_	_	_	0	0	15	44	

Note 1.Please order the tube packaging product, multiplying the tube packaging quantity.

Note 2.Please order the embossed tape packaging product according to reel number. (1 reel: 1000 pcs.)

Note 3. The absorption cap is attached to the embossed tape packaging product.

■Crimping Contact



Part Number	CL No.	Packaging Type	Quantity	Finish
DF13-2630SCF 536-0300-5		Reel	10,000	Tin plating
DF13-2630SCFA	536-0298-5	Reel	10,000	Gold plating

Applicable Cable (Tin Plating Annealed Copper Wire)

	Conductor Size (Wire construction)	Jacket Diameter
	AWG26(7 cores./0.16mm)	
	AWG28(7 cores./0.127mm)	φ0.65 to φ1.0mm
Ī	AWG30(7 cores./0.1mm)	

Note:If other cables are used instead of the applicable cable, please contact the Hirose sales department.

●Recommended Cable

Strip Length

UL1571

1.2 to 1.9mm


● Applicable Crimping Tool

Туре	Part Number	CL No.	Applicable Contact	
Applicator	AP105-DF13-2630S	901-4531-9	DF13-2630SCF/SCFA	
Press Main Unit	CM-105	901-0005-4		
Manual Crimping Tool	DF13-TB2630HC	550-0256-1	DF13-2630SCF	
Extraction Tool	DF-C-PO(B)	550-0179-2	DF13-2630SCF	

Note 1.If a trouble has occurred due to other tools, which are not designated by Hirose, Hirose won't guarantee any product.


Note 2. The manual crimping tool is used to sequentially cut the reel contact with carrier.


◆Application Pattern




● Embossed Carrier Tape Dimensions

- ●DF13B-*P-1.25V With boss
- ●DF13C-*P-1.25V Without boss





- DF13-*P-1.25H
- ●DF13A-*P-1.25H



Unit: mm

Product Type	Number of Contacts	A	В	С	D
DF13B-*P-1.25V	2, 3	16		7.5	16.4
DF13C-*P-1.25V	4 to 90	24		11.5	24.4
DF13-*P-1.25H	10 to 14	32	28.4	14.2	32.4
DF13A-*P-1.25H	15	44	40.4	20.2	44.4

Note: The 13 contacts is not serialized.

Precautions

