

ØF = Cable diameter

Order-No.	Shell Size / for No. of Contacts	B	C	D	ØF	H	U	V	W
FKH1-09P-5848	1 / 9	±0.1	±0.3	±0.3	min - max	±0.3	±0.4	±0.15	±0.2
FKH2-15P-5848	2 / 15	25	31.2	31.8	4.5 - 7	35	30.8	25	16.9
FKH3-25P-5848	3 / 25	33.3	40	32	4.5 - 7	34.7	39.1	33.3	25.2
		47.04	53.7	35	8 - 10.5	37.7	53	47.04	38.9


FKHY-xxP-5848

e.g. FKH3-25P-5848

*1) V for hood size 1, 2 or 3
 *2) xx No. of contacts 09, 15 or 25

RoHS compliant

Packing unit on supplement AM0409
 max. torque are 40 Ncm
 Part-No. 3 to 6 not mounted



reverse side
 1 : 1

No.	St.	Part	Type Description / Material	FRS1 / 5 4-40 / Brass	nickel plated
6	2	Knurled thumb screw	Steel	zinc plated	
5	2	Cable clamp screw	Steel	tin plated	
4	1	Cable clamp	Steel	zinc plated	
3	2	Shell screw	FKHY / PC+ABS	black	
2	1	Hood	FxxP0G1	Surface plating / Colour / Class	
1	1	D-Sub Connector	FxxP0G1		

REV.	DATE	CH.-NO.	REPLACEMENT FOR:
1			FKHY-xxP-5848



DWG. NO. FKHY-xxP-5848

REV. 1
 PAGES 1