

Datasheet

Stainless Steel Threaded Straight Coupler, 1/4 in G Female, 1/4 G Female

RS Stock number [3108624](#)



Features

- Double Female Sleeve BSPP
- Connection of 2 female ports
- Maximum working pressure: 150 bar
- Body: Stainless steel 316L

Specifications

- Working Temperature: -20 to 180 °C
- Connection 1: 1/4in G Female
- Connection 2: 1/4in G Female
- Connection Gender 1: Female
- Connection Gender 2: Female
- Fitting Direction: Straight
- Fitting Type: Coupler
- Thread Size 1: 1/4in
- Thread Size 2: 1/4in
- Thread Standard 1: G
- Thread Standard 2: G

Measurements

- C: G1/8
- F (mm): 17
- L1 (mm): 24
- Weight (kg): 0.023

