

VERDERFLEX[®]

OEM



EASY TUBE LOADING PUMP


MODEL: AU EZ d.c. PUMP
FIXED/VARIABLE SPEED

Easy tube loading peristaltic pump with 3-roller rotor as standard, stainless steel mounting plate and 12 vdc gear motor. Integral pump head drive shaft with ball dual ball race bearings.

Three available drive options combined with five tube sizes giving wide range of flow rates. Connection to a speed control circuit will give variable flow capability.

The quick and simple tube change only takes seconds.

For stackable options see MODEL AU ES.



Pump head : Polyamide, Acetal and Stainless Steel.

Gear motor : Permanent magnet

Power supply : 12 vdc 17W

Tube materials : Verderprene & Silicone

Weight : 1.3Kg

Easy tube loading pump d.c.					
Nominal flow rate ml/min					
Tube	0.8mm	1.6mm	3.2mm	4.8mm	6.3mm
60 rpm	4.6	16	64	140	225
100 rpm	7.7	28	108	235	375
150 rpm	12	42	162	352.5	562.5

Verder Ltd
 Unit 7 Carnival Park, Carnival Close, Basildon, SS14 3WN
 Tel: +44 (0) 1288 862 450, Fax: +44 (0) 1288 862 459
 Email: Basildon@verderflex.com

VERDER 

 www.verderflex.com