


NEUTRIK

- [Home](#)
- [About Us](#)
- Products**
 - Audio**
 - [Video](#)
 - [Lighting](#)
 - [Data Connectors](#)
 - [Industrial](#)
- [Support](#)
- [News](#)
- [Sitemap](#)

Search

 PRODUCTS ONLY

© Neutrik® AG
All rights reserved
[Legal Notices](#)



REAN TINY xlr Cable Connectors

[back](#)
RT3FC-B-W
Product

Gender female

Electrical

Contact resistance < 5 mΩ

Dielectric strength > 0.5 kVdc

Insulation resistance > 1 GΩ

Rated current per contact < 5 A

Mechanical

Cable O.D. 2.0 - 4.5 mm

Lifetime > 1000 mating cycles

 Wire size 0.22 mm²

Wire size 24 AWG

Wiring Solder contacts

RW / Straight no

Material

Bushing ABS

Contact plating Au

Contacts Bronze

Insert PA 6.6 30 % GF

Shell Zinc diecast (ZnAl4Cu1)

Shell plating Black

Strain relief PA6

Labeling no

Environmental

Solderability Complies with IEC 68-2-20

Temperature range -30 °C to +85 °C