

Data sheet

Commercial Art.No.: 70.350.1035.0

Hood BAS GOT GA 10 M20 A0

revos BASIC size 10 hood with cable gland M20, lateral cable entry, double locking lever

1011011010001010010101101
0100110110010110100101010
101001101100111001010010
101001101100111001010010
101001101100111001010010
1101010011011001011010010
10101010010101101010011
10101010010101101010011

**DIGITALIZATION
IN PROGRESS**

Commercial Art.No.	70.350.1035.0
EAN	4015573616776
Order Unit	1

Certificates / Approvals



Technical data

General

Housing material	Aluminium
Color	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

Construction	10
Model	male
Locking mechanism	Double locking levers
Cable entry	Sideways
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	20
Thread size PG	
Hinged lid	No
EMC-version	No
Length	73 mm
Width	43 mm
Height	53 mm

Classification

ECLASS 8.1	27440202
ETIM 7.0	EC000437
ETIM 6.0	EC000437

ETIM 5.0	EC000437
ETIM 4.0	EC000437
ETIM 3.0	EC000437