

SPECIFICATION

1. SCOPE

This specification is applied to the piezo-element.


2. SPECIFICATION

(at 25°C)

- 2.1 Resonant Frequency : 4.1 ± 0.5 KHz
- 2.2 Resonant Resistance : 500 Ω max
- 2.3 Capacitance : 20000 pF ± 30% at 100 Hz
- 2.4 Input Voltage : 30 Vp-p max
- 2.5 Operating Temperature : -20 ~ +50 °C
- 2.6 Storage Temperature : -20 ~ +60 °C

3. DIMENSION

: as per figure



<p>TOLERANCES UNLESS NOTED OTHERWISE</p> <p>.X ±</p> <p>.XX ±</p> <p>.XXX ±</p> <p>90° FORMED +2°</p> <p>ANGLES -1°</p> <p>FIRST ANGLE PROJECTION</p>	DRAWN		KEPO MODEL NO.	CUSTOMER			
	DESIGN		FT-27T-4.1BL	CUSTOMER NO.			
	CHECKED						
	APPROVED		DWG NO.	VER	1.0	SCALE	
	DATE	05.06.24	KP3.845.759	UNIT	mm	SHEET	
	CONTRACT NO.			KEPO CO.,LTD.			
AGENCY APPROVAL			TEL:(+86)574-88370330 FAX:(+86)574-88370329				