



Click [here](#) for the 3D model.

Dimensions

D	35mm MAX
T	33mm MAX
H	26mm MAX
LL	5mm +/-2mm
S	11mm NOM
S1	29mm NOM
Wire Size	1.3mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	140
Component Weight	49 g

General Information

Series	SCR25
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	70 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	500 VAC
Inductance	3.5 mH
Current	10.5 A
Temperature Range	-25/+120°C
DC Resistance	17 mOhms