


## SBCP-14HY2R2B

Aliases (UPIO14HY2R2B00)

KEMET, SBCP-14HY, Power, 2.2 uH, 30%, 5mm



Click [here](#) for the 3D model.

### Dimensions

D	12mm MAX
L	15mm MAX
S	5mm +/-0.5mm
LL	3.5mm +/-0.5mm
F	0.6mm NOM

### Packaging Specifications

Component Weight	6 g
Packaging	Bulk
Packaging Quantity	1500

### General Information

Series	SBCP-14HY
Style	Through-Hole
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Core	Ferrite

### Specifications

Inductance	2.2 uH
Inductance Tolerance	30%
Temperature Range	-20/+105°C
Shielded	No
Current	4.35 Amps
DC Resistance	0.02 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.