


## SMP253MA4150MTR24

Aliases (P101AA152M250V)

SMP253/P101, Film, Metallized Paper, Automotive Safety, 1500 pF, 20%, 250 VAC, 1500 VDC, 100°C, 5045, 6.5mm



Note: '()' correspond to the letters used in the product bulletin

Click [here](#) for the 3D model.

### Dimensions

Chip Size	5045
L	12.7mm +/-0.2mm
W	11.5mm +/-0.2mm
T	6.5mm +/-0.2mm
F	0.5mm NOM

### Packaging Specifications

Packaging	T&R
Packaging Quantity	600

### General Information

Series	SMP253/P101
Dielectric	Metallized Paper
Style	SMD Chip
RoHS	Yes
Termination	Tin
Safety Class	Y2
Qualifications	ENEC, cULus
AEC-Q200	Yes
THB Performance	No
Component Weight	1.6 g

### Specifications

Capacitance	1500 pF
Capacitance Tolerance	20%
Voltage AC	250 VAC
Voltage DC	1500 VDC
Temperature Range	-40/+100°C
Rated Temperature	100°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	2000 V/us